

EV-55 HEPA DT Electric Industrial HEPA Drum Top Vacuums





Industrial Vacuums for Hazardous Materials

Industrial Electrical **HEPA^{Plus}*** Drum Top Vacuums

PrestiVac **HEPA^{Plus}*** Drum Top vacuums are specifically designed to be used on standard 55 gallon drums. The dusts or liquids are collected directly into the standard 55 gallon drum. Absolute **HEPA^{Plus}*** filtration with an efficiency of 99.995% @ 0.2 micron captures all of the hazardous dust and ensures the exhaust air is clean, keeping the operator and the environment safe from exposure and contamination.

Features:

- Powerful Motor - High Performance
- All Stainless steel construction makes it a solid unit that is easy to clean and sterilize

- Complete with suction hose and accessories
- Stainless steel industrial cart assembly with ESD safe, conductive wheels
- Quiet operation with only xx dB
- Automatic suction shut off system when the collection tank is full of liquids (for Wet & Dry models)
- Stainless steel Drain valve assembly for easy emptying (for Wet & Dry models)

Filtration System:

- Washable, reusable main filter for dust and solids
- **HEPA^{Plus}** Filtration with an efficiency of 99.995% @ 0.2 micron. Testing Method: IEST RP-CC034.3. H14. MIL-STD 282 / A.S.T.M. - D2986-91. MPPS method EN 1822.

Applications:

- Debris
- Dust
- Machine shops
- Maintenance/House keeping
- Metal Chips

Specifications:

Model	EV1-55 HEPA DT	EV2-55 HEPA DT	
Air Watts	561	652	
Electricity	120v / 12a / 1488w	120v / 15a / 1790w	
Air Flow (CFM)	123	202	
Vacuum Pressure (H2O)	135	99	
Collection Type	Dry	Dry	
Capacity (gal)	55	55	
dB(A) @ 6 ft			

Included Accessories:

- Suction hose assembly
- Stainless steel double bend wand assembly
- Floor tool
- Crevice tool
- Round brush

Optional Accessories:

- Extension wand
- Single bend wand
- Flat tool
- Wall brush
- Dust extraction Arm

Filtration Options:

- **ULPA** Filtration with an efficiency of 99.9995% @ 0.12 micron. Testing Method: IEST RP-CC034.3. H15. MIL-STD 282 / A.S.T.M. - D2986-91. MPPS method EN 1822.
- Activated Carbon Filtration System to adsorb and neutralize fumes and vapors

If you have a special application or specific requirement, please feel free to contact us. As manufacturers, we can modify our units to meet your specific needs.

Hepa Vacuums, ELECTRIC